REVISION L

RECOMMENDED PCB LAYOUT FOR ERM8-XXX-XX.X-DV-XXXX-FOOTPRINT

5/16/2019 ECN-356379


DESIGNED & DIMENSIONED IN MILLIMETERS[INCHES]

NOTES:

PASTE-IN-HOLE TECHNOLOGY


Ø1.45[.057] NPTH (2 PLCS)

- 1. CONNECTOR ENVELOPE DIMENSIONS. OTHER COMPONENTS PLACED ON PCB SHALL AVOID THIS ZONE.
- THESE PLATED THROUGH HOLES AND STENCIL APERTURES NOT REQUIRED FOR ERM8-010-09.0-X-DV-EGPS.



ALL OPTIONS EXCEPT - EGPS
(-030 POSITION SHOWN)
(ALL DIMENSIONS ARE SYMMETRIC ABOUT THE CENTERLINE)

TABLE 1 "A" "B" "C" **POSITION** 3.20 [.126] -005 6.80 [.268] 10.00 [.394] -010 7.20 [.283] 10.80 [.425] 14.00 [.551] -011 8.00 [.315] 11.60 [.457] 14.80 [.583] -013 9.60 [.378] 13.20 [.520] 16.40 [.646] -020 15.20 [598] 18.80 [.740] 22.00 [.866] -025 19.20 [.756] 22.80 [.898] 26.00 [1.024] -030 23.20 [.913] 26.80 [1.055] 30.00 [1.181] -035 27.20 [1.071] 30.80 [1.213] 34.00 [1.339] -040 31.20 [1.228] 34.80 [1.370] 38.00 [1.496] -049 38.40 [1.512] 42.00 [1.654] 45.20 [1.780] -050 39.20 [1.543] 42.80 [1.685] 46.00 [1.811] -060 47.20 [1.858] 50.80 [2.000] 54.00 [2.126] -070 55.20 [2.173] 58.80 [2.315] 62.00 [2.441] -075 62.80 [2.472] 66.00 [2.598] 59.20 [2.331] -100 79.20 [3.118] | 82.80 [3.260] | 86.00 [3.386]



PROPRIETARY NOTE

THIS DOCUMENT CONTAINS CONFIDENTIAL AND PROPRIETARY INFORMATION AND ALL DESIGN, MANUFACTURING, REPRODUCTION, USE, PATENT RIGHTS AND SALES RIGHTS RARE EMPRESSY RESERVED BY SAMTEC, INC. THIS DOCUMENT SHALL HOT DE DECISOR, IN WHOLE OR PART, TO ANY UNAUTHORIZE D'RESON OR ENTITY NOR REPRODUCED, TRANSFERBED OR INCORPORATED IN ANY OTHER PROJECT IN ANY MANURE WITHOUT THE EXPRESS WRITTER CONSISTENCY OF SAMTEC. INC.



REVISION L

RECOMMENDED STENCIL LAYOUT FOR ERM8-XXX-XX.X-DV-XXXX-FOOTPRINT

NOTE: STENCIL TO BE 0.15[.006] THICK.




FIG 2 (-030 POSITION SHOWN) (ALL DIMENSIONS ARE SYMMETRIC ABOUT THE CENTERLINE)

DESIGNED & DIMENSIONED IN MILLIMETERS[INCHES]

TABLE 2		
POSITION	"A"	"C"
-005	3.20 [.126]	10.00 [.394]
-010	7.20 [.283]	14.00 [.551]
-011	8.00 [.315]	14.80 [.583]
-013	9.60 [.378]	16.40 [.646]
-020	15.20 [598]	22.00 [.866]
-025	19.20 [.756]	26.00 [1.024]
-030	23.20 [.913]	30.00 [1.181]
-035	27.20 [1.081]	34.00 [1.339]
-040	31.20 [1.228]	38.00 [1.496]
-049	38.40 [1.512]	45.20 [1.780]
-050	39.20 [1.543]	46.00 [1.811]
-060	47.20 [1.858]	54.00 [2.126]
-070	55.20 [2.173]	62.00 [2.441]
-075	59.20 [2.331]	66.00 [2.598]
-100	79.20 [3.118]	86.00 [3.386]

PROPRIETARY INFORMATION AND ALL DESIGN, MANUFACTURING, REPOLOCITION, USE, PATENT RIGHTS AND SALES RIGHTS ARE EXPRESSLY RESERVED BY SAMPLE, INC. THIS DOCUMENT SHALL NOT BE DISCLOSED, IN WHOLE OR PART, TO AN UNAUTHORIZED PRESON OR ENTITY ON ROOM REPRODUCED, TRANSFERRED OR INSTORMED IN ANY OTHER PROJECT IN ANY MANNER WITHOUT THE EXPRESS WRITTEN CORSENT OF SAMPLE, INC.






FIG 3
-EGPS AND -S OPTION
(-030 POSITION SHOWN)
(SAME AS FIG 1, EXCEPT AS SHOWN)
(ALL DIMENSIONS ARE SYMMETRIC ABOUT THE CENTERLINE)



TABLE 3

NOTE: STENCIL TO BE 0.15[.006] THICK.




FIG 4
-EGPS AND -S OPTION
(-030 POSITION SHOWN)
(SAME AS FIG 2, EXCEPT AS SHOWN)
(ALL DIMENSIONS ARE SYMMETRIC ABOUT THE CENTERLINE)

PROPRIETANY INFORMATION AND ALL DESIGN.

MANUFACTURING, BERDOULTON, USE, PATTENT RIGHTS
AND SALES RIGHTS, ARE EXPRESSLY RESERVED BY SAMTE,
INC. THIS DOCUMENT SHALL NOT BE DISCLOSED, BN WILL
OR PART, TO ANY UNALITHORIZED PRESON OR ENTITY NOR
REPRODUCED, TRANSFERRED OR INCOPPORATE DIS
WITHOUT ONE STANSFERRED OR INCOPPORATE DIS
WITHER ONSERTOR OF SAMTE, USE

