
REVISION E

RECOMMENDED PCB LAYOUT FOR PTHF


SS D DECKER 0/17/2007 ECN-81838



NOTE:

- 1. MAX HARDNESS OF COPPER LAYER: 150 KNOOP. 2. CONTACT SAMTEC FOR INSERTION TOOLING: P/N S-11297-XX

		E		
		Α	В	С
E	HASL	0.041	.036±.002	0.005 MAX
	GOLD	0.041	.038±.002	N/A
	SILVER	0.041	.038±.002	N/A
E	TIN	0.041	.038 <u>+</u> .002	N/A



SECTION "A"-"A"

PROPRIETARY NOTE

THIS DOCUMENT CONTAINS INFORMATION CONFIDENTIAL AND PROPRIETARY TO SAMTEC, INC. AND SHALL NOT BE REPRODUCED OR TRANSFERRED TO OTHER DOCUMENTS OR DISCLOSED TO OTHERS OR USED FOR ANY PURPOSE OTHER THAN THAT WHICH IT WAS OBTAINED WITHOUT THE EXPRESSED WRITTEN
CONSENT OF SAMTEC, INC.



PHONE: 812-944-6733 FAX: 812-948-5047 e-Mail: info@SAMTEC.com code: 55322

-sheet 1 of 1 ^J

F:\DWG\MISC\Mktg\Footprnt\PTHF-130-XX-X-Q-368-FOOTPRINT.SLDDRW