


# HIGH-SPEED EDGE CARD SYSTEMS

0.60 mm, 0.80 mm and 1.00 mm PITCH



#### **FEATURES & BENEFITS**

- Maximum Design Flexibility
- Up to 64 Gbps PAM4 performance
- PCI Express® 3.0, 4.0, 5.0 and 6.0
- Edge Rate<sup>®</sup> contacts optimized for signal integrity performance and high-cycle life
- Up to 200 positions available
- Vertical, right-angle, edge mount, pass-through orientations
- Power/signal combo, press-fit tails, rugged weld tabs, locks and latches
- Mating cable assemblies available



Rugged tucked beam technology (HTEC8)



Differential pair for increased speed (HSEC8-DP)



Custom designs allow for misalignment in the X-Y axes (HSEC1)

#### **KEY SPECIFICATIONS**

SERIES	PITCH	TOTAL POSITIONS	INSULATOR MATERIAL	CONTACT MATERIAL	OPERATING TEMP RANGE	CURRENT RATING	VOLTAGE RATING	LEAD-FREE SOLDERABLE
HSEC6	0.60 mm	56-168	Black LCP	Copper Alloy	-55 °C to +125 °C	1.9 A (2 pins)	240 VAC	Yes
HTEC8	0.80 mm	20-200	Black LCP	Copper Alloy	-55 °C to +125 °C	3.0 A (2 pins)	215 VAC	Yes
HSEC8	0.80 mm	18-200	Black LCP	BeCu	-55 °C to +125 °C	2.8 A (2 pins)	240 VAC	Yes
HSEC1	1.00 mm	20-140	Black LCP	Phosphor Bronze	-55 °C to +125 °C	2.2 A (2 pins)	215 VAC	Yes







#### (0.80 mm) .0315" PITCH • VERTICAL EDGE CARD SOCKET

HSEC8

POSITIONS PER ROW

09, 10,

13, 20, 25,

30, 37, 40,

49, 50, 60,

**70, 80, 100** (13, 25, 49 only

available with

-L or -L2 latching option; 09 only

available with

-L2 option; 37 only available with -L latching

option)

CARD **THICKNESS** 

-01

= (1.60 mm)

.062" thick card

-03

= (2.36 mm) .093" thick card

**PLATING** OPTION

= 10 µ" (0.25 µm) Gold on

contact area,

Matte Tin on tail

-S

= 30 µ" (0.76 µm) Gold on

contact area,

Matte Tin

on tail





OTHER OPTIONS

"X"R

Leave blank for

-K = Polyimide Pick & Place Pad

-BI = Board Locks;

-01 card only (Weld tab standard)

= Latching Option; -01 card only (13, 25, 37, 49 only) (Weld tab standard)

= ECDP Latching; -01 card only (09, 13, 25, 49 only) (For use with ECDP (Weld tab standard)

> -WT = Weld tab

Tray Packaging

**-TR** = Tape & Reel (09 - 70 only)

-FR = Full Reel Tape & Reel (must order max. quantities per reel; contact Samtec for quantity breaks) (09-70 only)


#### **HSEC8-DV**

#### Card Mates:

(1.60 mm) .062" card, (2.36 mm) .093" card, HSC8

#### Cable Mates: **ECDP**





10, 20, & 30 POSITIONS

## No. of Positions x (0.80) .0315 + (7.80) .307 (7.00) .276 (7.98) .314 (No. of Positions + 6) x (0.80) .0315 + (0.60) .024 09, 13, 25, 37 & 40 **THRU 100 POSITIONS**

#### **OTHER SOLUTIONS**

For complete edge card system with cards and sockets. visit samtec.com?RU8

> For a card to mate with an HSEC8 socket, visit samtec.com?HSC8



### Note:

Some sizes, styles and options are non-standard, non-returnable.

POSITIONS PER ROW	A	В	
09*†	(4.50) .177	(11.80) .465	
13*†	(6.10) .240	(15.00) .591	
25*†	(6.10) .240	(24.60) .969	
37†	(18.10) .713	(34.20) 1.346	
40	(18.90) .744	(36.60) 1.441	
49*†	(22.90) .902	(43.80) 1.724	
50	(22.90) .902	(44.60) 1.756	
60	(26.90) 1.059	(52.60) 2.071	
70†	(26.90) 1.059	(60.60) 2.386	
80†	(26.90) 1.059	(68.60) 2.701	
100†	(26.90) 1.059	(84.60) 3.331	

Positions where no dimensions are given do not have keying feature.

- \* Mates with ECDP Series
- † Available with -01 Card Only

CABLE	CONNECTOR
ECDP-04	HSEC8-109-L2
ECDP-08	HSEC8-113-L2
ECDP-16	HSEC8-125-L2
ECDP-32	HSEC8-149-L2

View complete specifications at: samtec.com?HSEC8-DV