



**(1,27mm) .050"**  
**CFT, CFS SERIES**

# COMPACT FLASH TERMINALS & SOCKETS

### SPECIFICATIONS

For complete specifications and recommended PCB layouts see [www.samtec.com?CFT](http://www.samtec.com?CFT)

**Insulator Material:** Black Liquid Crystal Polymer

**Terminal Material:** Phosphor Bronze

**Plating:** Sn or Au over 50µ" (1,27µm) Ni

**Current Rating:** 2A @ 80°C ambient

**Operating Temp Range:** -55°C to +105°C with Tin; -55°C to +125°C with Gold

**Max Processing Temp:** 230°C for 60 seconds, or 260°C for 20 seconds 3x

**Lead-Free Solderable:** Yes

**SMT Lead Coplanarity:** (0,15mm) .006" max

**RoHS Compliant:** Yes

**APPLICATION**

**Note:** Some lengths, styles and options are non-standard, non-returnable.

**CFT - 125 - LEAD STYLE - PLATING OPTION - D - RA - CARD LENGTH - SL**

Mates with: CFS

Specify LEAD STYLE from chart

**-L** = 10µ" (0,25µm) Gold on post, Matte Tin on tail

**-S** = 30µ" (0,76µm) Gold on post, Matte Tin on tail

**-01** = (25,40mm) 1.00" Card Length

**-02** = (50,80mm) 2.00" Card Length

POSITION NUMBER	C (POST)
25, 26	(3,50) .138
01, 13, 38, 50	(5,00) .197
ALL OTHERS	(4,25) .167

LEAD STYLE	Y
-01	(6,35) .250
-02	(8,89) .350

**-RA OPTION**

### SPECIFICATIONS

For complete specifications and recommended PCB layouts see [www.samtec.com?CFS](http://www.samtec.com?CFS)

**Insulator Material:** Black Liquid Crystal Polymer

**Contact Material:** BeCu

**Plating:** Au or Sn over 50µ" (1,27µm) Ni

**Current Rating:** 1A

**Operating Temp Range:** -55°C to +125°C

**Contact Resistance:** 10 mΩ max

**Insertion Depth:** (3,05mm) .120" min

**Insertion Force:** (Single contact only) 3.3oz (0,92N) avg.

**Withdrawal Force:** (Single contact only) 2.5oz (0,70N) avg.

**Max Processing Temp:** 230°C for 60 seconds, or 260°C for 20 seconds 3x

**Lead-Free Solderable:** Yes

**SMT Lead Coplanarity:** (0,10mm) .004" max

**RoHS Compliant:** Yes

**CFS - 1 - NO. PINS PER ROW - CARD THICKNESS - PLATING OPTION - D**

Mates with: CFT

**Note:** Some sizes, styles and options are non-standard, non-returnable.

**-01** = (0,80mm) .031" thick board

**-02** = (1,60mm) .062" thick board

**-L** = 10µ" (0,25µm) Gold on contact, Matte Tin on tail

**-S** = 30µ" (0,76µm) Gold on contact, Matte Tin on tail

CARD THICKNESS	A	B	C
-01	(1,02) .040	(1,79) .070	(3,12) .123
-02	(1,70) .067	(2,46) .097	(2,77) .109

**TIGER EYE CONTACT™**

*Due to technical progress, all designs, specifications and components are subject to change without notice.*

[WWW.SAMTEC.COM](http://WWW.SAMTEC.COM)