

ACCLIMATE



IP68 SEALED USB CABLE PLUG

SPECIFICATIONS


For complete specifications see www.samtec.com?RCU

Insulator Material:
Glass Filled Thermoplastic
Contact Material:
Phosphor Bronze
Current Rating:
4.2 A per pin
(1 pin powered)
Operating Temp Range:
-20 °C to +80 °C
Shield Material:
Phosphor Bronze
Wire:
20 AWG (Power)
25 AWG (Signal)
28 AWG (Drain)

Mates with: RPCU, RPBU

(26.09)

-AMS



 \Box

-AM

(15.90) .626

DUST CAPS

-AMS = DCA-RCU-01-01-A -BMS = DCA-RCU-01-01-B

ALSO AVAILABLE (MOQ REQUIRED)

- Other wire lengths
- End option 2 with -AMS, -BMS or -BM

WIRE LENGTH END 2 END 1 **RCU PLATING OPTION** OPTION -01.00 = (1 m) 40" Cable -AM = USB A Type, Not Sealed -AMS USB A Type, -G = 30 μ" (0.76 μm) Gold on contact, Sealed Nickel on shell -02.00 -BMS -BC = (2 m) 79" Cable USB B Type, Sealed = Blunt Cut Standard lengths Cable Length + (35.6) 1.40