





MUSBS SERIES

IP68 SEALED MINI USB PORT

SPECIFICATIONS

For complete specifications and recommended PCB layouts see www.samtec.com?MUSBS

Insulator Material:

Black High Temperature Thermoplastic Contact Material:

Phosphor Bronze Shell Material:

Phosphor Bronze

Phosphor Bronze
Plating:
Gold on Mating Area,
Nickel on Shell, Tin on Tails
Operating Temp Range:
-50 °C to +85 °C
Current Rating:
31 A per pin

3.1 A per pin (1 pin powered per row)

Voltage Rating:

Minimum Cycles:

RoHS Compliant:

Lead-Free Solderable:



