

FIG 1 MPTC-V MATED WITH MPSC-V




FIG 2 MPTC-V MATED WITH MPSC-RA

NOTES: 1. ALL DIMENSIONS BASED ON NOMINAL VALUES FOR SAMTEC

RECOMMENDED PCB LAYOUTS. 2. ALTHOUGH MAX DIMENSIONS ARE LISTED, SAMTEC RECOMMENDS

FULLY MATING COMPONENTS.

3. MAXIMUM ALLOWABLE ANGLE AT FULLY MATED NOMINAL CONDITIONS.

MPXC MATED VIEWS

DESIGNED & DIMENSIONED IN MILLIMETERS[INCHES]

TABLE 1										
	MPT	C-V	SIGNAL F	PIN WIPE	POWER PIN WIPE					
MPSC-V	"A" FULLY MATED	"A" MAX	MAX CONTACT WIPE	MIN CONTACT WIPE	MAX CONTACT WIPE	MIN CONTACT WIPE				
-7.70	13.88 [0.546]	14.18 [0.558]	1.32 [0.052]	1.02 [0.040]	2.45 [0.096]	2.15 [0.085]				
*-9.70	15.88 [0.625]	16.18 [0.637]	1.32 [0.052]	1.02 [0.040]	2.45 [0.096]	2.15 [0.085]				
(* = NOT TOOLED)										

NOT TOOLED)

TABLE 2									
		MPT	C-V		SIGNAL PIN WIPE		POWER PIN WIPE		
MPSC-RA	"B" FULLY MATED	"B" MAX	"C" FULLY MATED	"C" MAX	MAX CONTACT WIPE	MIN CONTACT WIPE	MAX CONTACT WIPE	MIN CONTACT WIPE	
-01	12.65 [0.498]	13.28 [0.523]	21.36 [0.841]	21.99 [0.866]	1.65 [0.065]	1.02 [0.040]	2.45 [0.096]	1.82 [0.072]	

PROPRIETARY NOTE THIS DOCUMENT CONTAINS INFORMATION CONFIDENTIAL AND PROPRIETARY TO CONNIDENTIAL AND PROPRIETARY TO SAMTEC, INC, AND SHALL NOT BE REPRODUCED OR TRANSFERRED TO OTHER DOCUMENTS OR DISCLOSED TO OTHERS OR USED FOR ANY PURPOSE OTHER THAN THAT WHICH IT WAS OBTAINED WITHOUT THE EXPRESSED WRITTEN CONSENT OF SAMTEC, INC.



F:\DWG\MISC\Mktg\MPXC Mated Document-mkt.SLDDRW

code 55322 -SHEET 1 OF 2

REVISION B

MPXC MATED VIEWS




TABLE 3										
		MPT	C-RA		SIGNAL PIN WIPE		POWER PIN WIPE			
MPSC-V	"D" FULLY MATED	"D" MAX	"E" FULLY MATED	"E" MAX	MAX CONTACT WIPE	MIN CONTACT WIPE	MAX CONTACT WIPE	MIN CONTACT WIPE		
-7.70	8.60 [0.339]	8.90 [0.350]	18.20 [0.717]	18.50 [0.728]	1.32 [0.052]	1.02 [0.040]	2.45 [0.096]	2.15 [0.085]		
*-9.70	10.60 [0.417]	10.90 [0.429]	20.20 [0.795]	20.50 [0.807]	1.32 [0.052]	1.02 [0.040]	2.45 [0.096]	2.15 [0.085]		
(* = NOT T	(* = NOT TOOLED)									

FIG 3 MPTC-RA MATED WITH MPSC-V





TABLE 4										
MPSC-RA		MPT	C-RA		SIGNAL PIN WIPE		POWER PIN WIPE			
	"F" FULLY MATED	"F" MAX	"G" FULLY MATED	"G" MAX	MAX CONTACT WIPE	MIN CONTACT WIPE	MAX CONTACT WIPE	MIN CONTACT WIPE		
-01	7.37 [0.290]	8.00 [0.315]	25.68 [1.011]	26.31 [1.036]	1.65 [0.065]	1.02 [0.040]	2.45 [0.096]	1.82 [0.072]		

PROPRIETARY NOTE



EKOPKIELAKT NOIE THIS DOCUMENT CONTAINS INFORMATION CONFIDENTIAL AND PROPRIETARY TO SAMTEC, INC. AND SHALL NOT BE REPRODUCED OR TRANSFERRED TO OTHER DOCUMENTS OR DISCLOSED TO OTHERS THAN THAT WHICH IT WAS OBTAINED WITHOUT THE EXPRESSED WRITTEN CONSENT OF SAMTEC, INC. 520 PARK EAST BLVD, NEW ALBANY, IN 47150 PHONE: 812-944-6733 FAX: 812-948-5047 e-Mail info@SAMTEC.com code 55322 SHEET 2 OF 2