




MATED  
CABLE  
HEIGHTS



SERIES	PITCH	MATES WITH	VERTICAL	HORIZONTAL
6QCD	.635mm (.025")	QMS/QFS	.950" (24.13mm)	.595" (15.113mm)
6QDP	.635mm (.025")	QMS-DP/QFS-DP	.950" (24.130mm)	.595" (15.113mm)
6QDPS	.635mm (.025")	QMSS-DP/QFSS-DP	.950" (24.130mm)	.595" (15.113mm)
EEDP	.8mm (.0315")	MEC8-RA/HSEC8	.708" (17.983mm)	.266" (6.756mm)
EQCD	.8mm (.0315")	QTE/QSE	.652" (16.561mm)	.365" (9.271mm)
EQDP	.8mm (.0315")	QTE-DP/QSE-DP	.652" (16.561mm)	.365" (9.271mm)
EQRD	.8mm (.0315")	QRF8/QRM8	N/A	.570" (14.473 mm)
EQRF	.8mm (.0315")	QTE/QSE	1.774" (45.053 mm)	.299" (7.582 mm)
EQRP	.8mm (.0315")	QRF8-DP/QRM8-DP	N/A	.570" (14.473 mm)
EQSD	.8mm (.0315")	QTE/QSE	.652" (16.561mm)	.365" (9.271mm)
ERCDA	.8mm (.0315")	ERF8(-L)	.912" (23.163mm)	.584" (14.826mm)
ERDP	.8mm (.0315")	ERM8/ERF8	.912" (23.163mm)	.584" (14.826mm)
FCC8	.8mm (.0315")	FCS8	N/A	.213" (5.403 mm)
FFTP	.5mm (.0197")	FTS/FTSH	N/A	.315" (8.001 mm)
FHSC	.050" (1.27mm)	SFM/TFM	.812" (20.620mm)	.428" (10.87mm)
HBCD	.5mm (.0197")	BTH/BSH	.652" (16.561mm)	.365" (9.271mm)
HHSC	.100" (2,54mm)	SSQ/HTSS	.981" (24.920mm)	.615" (15.621mm)
HQCD	.5mm (.0197")	QTH/QSH	.652" (16.561mm)	.365" (9.271mm)
HQDP	.5mm (.0197")	QTH-DP/QSH-DP	.652" (16.561mm)	.365" (9.271mm)
HQDP	.5mm (.0197")	QTH-DP/QSH-DP	.785" (19.939mm)	.369" (9.373mm)
MICD	.635mm (.025")	MIT/MIS	.652" (16.561mm)	.365" (9.271mm)
Q2DA	.635mm (.025")	QMS	.798" (20.279 mm)	N/A
SQCD	.635mm (.025")	QTS/QSS	.652" (16.561mm)	.365" (9.271mm)
THSC	2mm (.0787")	SQT/LTMM	N/A	.492" (12.497mm)