



# PLATING SPECIFICATIONS (SEE TABLE 1)

MATTE TIN CONTACT AND TAIL

10µ" LIGHT SELECTIVE GOLD IN CONTACT AREA MATTE TIN ON TAIL

3µ" FLASH SELECTIVE GOLD CONTACT AREA, MATTE TIN ON TAIL

30µ" SELECTIVE GOLD IN CONTACT AREA, MATTE TIN ON TAIL

30µ" HEAVY GOLD IN CONTACT AREA 3u" GOLD ON TAIL

-SM: 30µ" SELECTIVE GOLD IN CONTACT AREA, MATTE TIN ON TAIL

-TM: MATTE TIN CONTACT AND TAIL

-LM: 10µ" LIGHT SELECTIVE GOLD IN CONTACT AREA MATTE TIN ON TAIL

-FM: 3µ" FLASH SELECTIVE GOLD IN CONTACT AREA, MATTE TIN ON TAIL

-LTL: 10µ'' LIGHT SELECTIVE GOLD IN CONTACT AREA, TIN LEAD (90/10 +/-5%) ON TAIL

POLARIZING OPTION INSERT PK-06-N INTO SPECIFIED POS AND BREAK OFF TAB (NOT AVAILABLE FOR -BE OPTION)

## **ENTRY SPECIFICATION**

-DE: DUAL ENTRY (SEE TABLE 1)

-TE: TOP ENTRY (SEE TABLE 1)

-HE: HORIZONTÀL ENTRY (SEE TABLE 1)

-PE: PASS-THROUGH ENTRY (SEE TABLÉ 1)


-DE-BE: (SEE TABLE 1)

-PE-BE: (SEE TABLE 1)

## **BODY SPECIFICATION**

-S: SINGLE ROW (SEE TABLE 1)

-D: DOUBLE ROW (SEE TABLE 1)



CONTACT #1 .16 [4.1] 〈C〉 -2° MAX SWAY -2° MAX SWAY IN EITHER DIRECTION <u>-DE/-DE-BE</u> FIG 1(SEE NOTE 11) SECTION "B"-"B" SECTION "A"-"A"

BCS-1XX-X-D-DE

POSITION 01 (-DE TAIL ORIENTATION) (-TE TAIL ORIENTATION)

### NOTES:

POSITION 01

1. © REPRESENTS CRITICAL DIM. FOR STATISTICAL PROCESS CONTROL.

2. MINIMUM PUSHOUT FORCE TO BE: 1 LB.

3. [] DIMENSIONS ARE IN MILLIMETERS.

4. MINIMUM WALL THICKNESS ON CUT PARTS: .009 [0.23].

5. CUT PARTS TO BE SYMMETRICAL ABOUT &

6. 1st POSITION WILL ALWAYS POINT UP ON TOP VIEW AS SHOWN.


7. 1 THROUGH 4 POSITIONS ARE TO BE LAYER PACKAGED, 5 THROUGH 50 POSITIONS ARE TO BE TUBED FOR ALL ENTRY SPECIFICATION EXCEPT BCS-S-HE AND BCS-D-HE. FOR BCS-S-HE AND BCS-D-HE. 1 THROUGH 3 POSITIONS ARE TO BE LAYER PACKAGED, 4 THROUGH 50 POSITIONS ARE TO BE TUBED.

8. DAMAGE TO THE CUT SURFACE CAN NOT EFFECT LEAD-IN OF THE CORES.

9. MAXIMUM VARIATION WITHIN A ROW: .006 [0.15]. MAXIMUM VARIATION FROM ROW TO ROW: .012 [0.30].

MAXIMUM CUT FLASH: .015 [0.38]

11. CHAMFERED END-WALLS MAY OR MAY NOT BE PRESENT ON ONE OR BOTH ENDS OF FINISHED GOOD.



(-HE TAIL ORIENTATION)

BCS-1XX-X-S-DE

DIMENSIONS ARE IN INCHES. TOLERANCES ARF: DECIMALS ANGLES

.XX: ±.01[0.3] .XXX: ±.005[0.13] .XXXX: ±.0020[0.051]

UNLESS OTHERWISE SPECIFIED

THIS DOCUMENT CONTAINS CONFIDENTIAL AND PROPRIETARY INFORMATION AND ALL DESIGN MANUFACTURING, REPRODUCTION, USE, PATENT RIGHTS
AND SALES RIGHTS ARE EXPRESSLY RESERVED BY SAMTEC, INC. THIS DOCUMENT SHALL NOT BE DISCLOSED, IN WHOLE OR PART, TO ANY UNAUTHORIZED PERSON OR ENTITY NOR REPRODUCED, TRANSFERRED OR INCORPORATED IN ANY OTHER PROJECT IN ANY MANNER WITHOUT THE EXPRESS


PROPRIETARY NOTE

SHEET SCALE: 2:1

DO NOT SCALE DRAWING

INSULATOR: GLASS FILLED LCP UL 94 VO, COLOR: BLACK CONTACT: PHOS. BRONZE

F:\DWG\MISC\MKTG\BCS-1XX-XXX-X-XX-XXX-MKT.SLDDRW



(-PE TAIL ORIENTATION)



PHONE: 812-944-6733 FAX: 812-948-5047 e-Mail info@SAMTEC.com

DESCRIPTION


**BOX CONNECTOR SOCKET STRIP** 


DWG. NO

S-1XX-XXX-X-XX-XXX


BY: KOLB

09/12/1991 | SHEET 1 OF 3





IN-PROCESS BCS-1XX-X-S-PE (SAME FOR -BE)	
IN-PROCESS 1	



-S-PE-BE: (SAME AS -S-PE EXCEPT AS SHOWN)

-D-PE-BE: (SAME AS -D-PE)

PART NUMBER	TUBE	PLUG
BCS-S-DE	PT-3-24-01-01	TP-03 (2)
BCS-D-DE	PT-1-24-01-15	TP-03 (2)
BCS-S-TE	PT-1-24-01-24	TP-24 (2)
BCS-D-TE	PT-1-24-01-22	TP-03 (2)
BCS-S-HE	PT-1-24-04-38	TP-03 (2)
BCS-D-HE	PT-1-24-01-127	TP-07 (2)
BCS-S-PE	PT-1-24-20-09	TP-03 (2)
BCS-D-PE	PT-1-24-01-15	TP-03 (2)
BCS-S-DE-BE	PT-3-24-01-01	TP-03 (2)
BCS-D-DE-BE	PT-1-24-01-15	TP-03 (2)
BCS-S-PE-BE	PT-1-24-20-09	TP-03 (2)
BCS-D-PE-BE	PT-1-24-01-15	TP-03 (2)

\* PROPRIETARY NOTE

THIS DOCUMENT CONTAINS CONFIDENTIAL AND PROPRIETARY INFORMATION AND ALL DESIGN. 
MANUFACTURING, REPRODUCTION, USE, PATENT RIGHTS 
AND SALES RIGHTS ARE EXPRESSLY RESERVED BY SAMITEC, 
INC. THIS DOCUMENT SHALL NOT BE DISCLOSED, IN WHOLE 
OR PART, TO ANY UNAULTHORISED PERSON OR ENTITY NOR 
REPRODUCED, TRANSFERBED OR INCORPORATED IN ANY 
OTHER PROJECT IN ANY MANUFAL WITHOUT THE EXPLOSE.

WRITTEN CONSENT OF SAMTEC, INC.

DO NOT SCALE DRAWING

SHEET SCALE: 2:1

. | [

e-Mail info@SAMTEC.com code 55322

DESCRIPTION:

BOX CONNECTOR SOCKET STRIP

520 PARK EAST BLVD, NEW ALBANY, IN 47150

PHONE: 812-944-6733 FAX: 812-948-5047

DWG. NO. BCS-1XX-XXX-X-XXXXXX

BY: KOLB 09/12/1991 SHEET 3 OF 3

F:\DWG\MISC\MKTG\BCS-1XX-XXX-X-XXX-MKT.SLDDRW