

NOTES:

DO NOT

SCALE FROM

THIS PRINT

- 1. PREPRESENTS A CRITICAL DIMENSION.
- 2. NOTE DELETED.
- 3. MINIMUM PUSHOUT FORCE: .5 LB.
- 4. WILL LOSE TWO POSITIONS FOR EVERY CUT MADE. MAXIMUM CUT FLASH TO BE .010 [0.25] WITH NO FLASH IN HOLES OR EXTENDING BELOW LEADS.
- 5. NOTE DELETED.
- 6. MAXIMUM BURR ALLOWANCE: .003 [0.08]
- 7. ENDWALL AFTER CUTTING: .0115±.0025 [0.292±0.064]
- 8. VOIDS ON TOP SURFACE TO BE LOCATED AT VENDOR DISCRETION TO CONTROL PART WARPAGE.
- 9. -TR OPTION ORDERS INVOLVING PARTIAL REEL QUANTITIES MAY BE PACKAGED ACCORDING TO THE SAMTEC PACKAGING EFFICIENCY STANDARDS (SPES) FOUND ON WWW.SAMTEC.COM.
- 10. -FR OPTIONS WILL BE SHIPPED AT THE MAX QUANTITY PER REEL, BASED ON OPTIONS SELECTED.

UNLESS OTHERWISE SPECIFIED, DIMENSIONS ARE IN INCHES.

TOLERANCES ARE: DECIMALS ANGLES

.XX: ±.01[0.3] .XXX: ±.005[0.13] .XXXX: ±.0020[0.051]

PROPRIETARY NOTE THIS DOCUMENT CONTAINS CONFIDENTIAL AND PROPRIETARY INFORMATION AND ALL DESIGN AND SALES RIGHTS ARE EXPRESSLY RESERVED BY SAMTED INC. THIS DOCUMENT SHALL NOT BE DISCLOSED, IN WHOLE OR PART. TO ANY LINAUTHORIZED PERSON OR ENTITY NOR REPRODUCED, TRANSFERRED OR INCORPORATED IN ANY

OTHER PROJECT IN ANY MANNER WITHOUT THE EXPRESS SHEET SCALE: 5:1

DO NOT SCALE DRAWING

CONTACT: BeCu 190 ALLOY [TM04]

THICKNESS: .007[0.18]REF

INSULATOR: LCP, UL 94 VO, COLOR: BLACK

.8MM x 1.2MM C.L. SOCKET STRIP ASSEMBLY DWG. NO.

520 PARK EAST BLVD, NEW ALBANY, IN 47150

PHONE: 812-944-6733 FAX: 812-948-5047

e-Mail info@SAMTEC.com

CLE-1XX-XX-X-DV-XX

c:\enterprisevault\DWG\MISC\MKTG\CLE-1XX-XX-X-DV-XX-MKT.SLDDRW

BY: PURVIS

10/23/95

SHEET 1 OF 2

code 55322

