
REVISION BX

DO NOT SCALE FROM THIS PRINT

l		TABLE 1								
	STYLE	"B"	"C"	"D" MAX	"E"	"F"	TERMINAL			
	-01	.230[5.84]	.280[7.11]	.208[5.28]	.445[11.30]	.165 [4.19]	T-1S6-16-X-2			
	-02	.320[8.13]	.370[9.40]	.205[5.20]	.530[13.46]	.165 [4.19]	T-1S6-08-X-2			
	-03	.420[10.67]	.470[11.94]	.205[5.20]	.630[16.00]	.165 [4.19]	T-1S6-15-X-2			
	-04	.120[3.05]	.270[6.86]	.208[5.28]	.335[8.51]	.050 [1.27]	T-1S6-21-X-2			
	-05	.075[1.91]	.270[6.86]	.223[5.66]	.300[7.62]	.050 [1.27]	T-1S6-18-X-2			



T-1S6-XX-X-2



LEAD STYLE SEE TABLE 1


PLATING SPECIFICATION

- -T: MATT TIN CONTACT AND TAIL -S: SELECTIVE, 30 Au / 50 Ni MIN ON CONTACT, MATTE TIN TAIL
- -G: GOLD, 10 Au / 50 Ni MIN ON CONTACT, 3 Au / 50 Ni MIN ON TAIL
- -L: LIGHT SELECTIVE, 10 Au / 50 Ni MIN ON CONTACT, MATTE TIN ON TAIL
- -F: FLASH SELECTIVE, 3 Au / 50 Ni MIN ON CONTACT, MATTE TIN TAIL
- -H: HEAVY GOLD, 30 Au / 50 Ni MIN ON CONTACT, 3 Au / 50 Ni MIN ON TAIL
- -TL: TIN / LEAD (90/10+/-5%) CONTACT AND TAIL [LEAD STYLE'-01 & -02 ONLY]
- -STL: SELECTIVE, 30 Au / 50 Ni MIN ON CONTACT, TIN/LEAD (90/10+/-5%) TAIL [LEAD STYLE -01 & -02 ONLY]

.025 [0.64] SQ

REF(TYP)

- -TM: MATTE TIN CONTACT AND TAIL -SM: SELECTIVE, 30 Au / 50 NI MIN ON CONTACT, MATTE TIN TAIL
- -LM: LIGHT SELECTIVE, 10 Au / 50 Ni MIN ON CONTACT, MATTE TIN TAIL
- -FM: FLASH SELECTIVE, 3 Au / 50 Ni MIN ON CONTACT, MATTE TIN TAIL
- -SS: STRIPE SELECTIVE, 30 Au / 50 Ni MIN ON CONTACT, MATTE TIN TAIL (SEE NOTE 9)



OPTION #3

- -P: PICK & PLACE PAD (SEE FIG. 3) [USE PPP-07] (4 POS MINIMUM OR -02 & -03 POS WITH -TR & -FR) (SEE NOTE 7)
- -TR: TAPE & REEL (SEE NOTE 7 & 12) (-02 THRU -22 POS)
- -FR: FULL REEL QTY. TAPE & REEL (-02 THRU -22 POS) (SEE NOTE 7 & 11)


POLARIZED POSITION: SPECIFY PIN OMITTED

OPTION #1

- -LC: LOCKING CLIP (SEE FIG. 1) (SEE NOTE 8) [USE LC-08-TM-02] (-03 THRU -36 POS: 2 PER STRIP, -02 POS: 1 PER STRIP)
- -A: ALIGNMENT PIN (SEE FIG. 2)

ROW SPECIFICATION

-SV: SINGLE VERTICAL (USE TSM-XX-SV-XX)



IN-PROCESS .002[.05] (SEE TABLE 1 & NOTE 5) "E" REF

NOTES:

- REPRESENTS A CRITICAL DIMENSION. 2. COPLANARITY TO BE WITHIN .006[.15].
- 3. BURR ALLOWANCE: .0015[.038] MAX.
 4. MAXIMUM CUT FLASH: .015[.38] MAXIMUM ON TOP & SIDES OF BODY AND .030[.76] MAXIMUM ON SURFACE MOUNT SIDE OF BODY.

2° MAX SWAY

(EITHER DIRECTION)

(CONTACT AREA

.099 [2.51]

- 5. POST HEIGHT VARIATION BETWEEN ANY TWO PINS: .005[.13] MAXIMUM.
- 6. MAXIMUM ALLOWABLE BOW: .002[.05] INCH/INCH AFTÈR ÁSSEMBLY. 7. LEADS MAY NOT BE VISIBLE FOR CUSTOMER VISUAL INSPECTION WITH -P OPTION ON SMALLER POSITIONS PARTS.
- 8. DUE TO THE HIGH AMOUNT OF INSERTION FORCE NEEDED, THE -LC OPTION IS NOT COMPATIBLE WITH AUTO PLACEMENT. SAMTEC RECOMMENDS MANUAL PLACEMENT FOR ALL ASSEMBLIES WITH THE -LC OPTION.

- 9. -01 LEAD STYLE ONLY, MATES WITH SSW, SSQ, BCS, SSM, ESW, ESQ.
 10. MINIMUM PUSHOUT FORCE: 2LB. [8.90 N].
 11. -FR OPTIONS WILL BE SHIPPED AT THE MAX QUANTITY PER REEL, BASED ON OPTIONS SELECTED. 12. -TR OPTION ORDERS INVOLVING PARTIAL REEL QUANTITIES MAY BE PACKAGED ACCORDING TO THE SAMTEC PACKAGING EFFICIENCY STANDARDS (SPES) FOUND ON WWW.SAMTEC.COM.

.010 0.25 REF

(No OF POS -2) x .100[2.54]

UNLESS OTHERWISE SPECIFIED. DIMENSIONS ARE IN INCHES. TOLERANCES ARE:

FIG 1

TSM-112-02-XXX-SV-LC SHOWN

 $\langle C \rangle$

"B" ± .008[.20]

(SEE TABLE

& NOTE 5)

.100 [2.54] REF

LC-08-TM-02

MAX SWAY

(EITHER DIRECTION)

DECIMALS **ANGLES** .XX: ±.01 [.3] .XXX: ±.005 [.13] 2 ° .XXXX: ±.0020 [.051]

THIS DOCUMENT CONTAINS CONFIDENTIAL AND PROPRIETARY INFORMATION AND ALL DESIGN, MANUFACTURING, REPRODUCTION, USE, PATENT RIGHTS AND SALES RIGHTS ARE EXPRESSLY RESERVED BY SAMTEC, INC. THIS DOCUMENT SHALL NOT BE DISCLOSED, IN WHOLE OR PART, TO ANY UNAUTHORIZED PERSON OR ENTITY NOR REPRODUCED, TRANSFERRED OR INCORPORATED IN ANY OTHER PROJECT IN ANY MANNER WITHOUT THE EXPRESS

MATERIAL: DO NOT SCALE DRAWING SHEET SCALE: 2.5:1 INSULATOR:

LCP, UL 94 VO COLOR: BLACK

TERMINAL: PHOS BRONZE

F:\DWG\MISC\MKTG\T\$M-1XX-XXX-SV-XX-XXX-XXX-MKT.SLDDRW

520 PARK EAST BLVD, NEW ALBANY, IN 47150 PHONE: 812-944-6733 FAX: 812-948-5047 e-Mail info@SAMTEC.com code 55322

DESCRIPTION

SINGLE ROW .100 SMT ASSEMBLY

DWG. NO TSM-1XX-XX-XXX-SV-XX-XXX-XX

BY: DEAN P

8/21/2002 SHEET 1 OF 2




TABLE 3: PICK	TABLE 3: PICK & PLACE PAD ALIGNMENT		
POSITION	TOLERANCE		
-02 THRU -04	"A"+/010		
-05 THRU -50	"A"+/020		

FIG 2 -A: ALIGNMENT PIN OPTION TSM-112-02-X-SV-A SHOWN [DIFFERENT AS SHOWN, OTHERWISE SAME AS FIG 1] -SEE TABLE 2 .100 [2.54] REF $\emptyset.062[1.57]$ (No OF POS -2) x .100[2.54] REF → REF **TABLE 2: ALIGNMENT PIN BODY POSITION USE BODY**

TSM-03-SV-A

TSM-XX-SV-X

-3

-02 & -04 THRU -50

PACKAGING TABLE						
STYLE	OPTION	TUBE	PLUG			
-01		PT-1-24-02-29 (SEE NOTE 3)	TP-24			
-02, -04, -05		PT-1-24-02-29 (SEE NOTE 3)	TP-24			
-01, -02, -04, -05	-LC, -A	PT-1-24-02-29 (SEE NOTE 3)	TP-24			
-01, -04, -05	-P	PT-1-24-05-29	TP-03			
-01, -04, -05	-LC-P, -A-P	PT-1-24-05-29	TP-03			
-02	-P	PT-1-24-13-29	TP-03			
-02	-LC-P, -A-P	PT-1-24-13-29	TP-03			
-03		PT-1-24-10-29 (SEE NOTE 3)	TP-24			
-03	-LC, -A	PT-1-24-10-29 (SEE NOTE 3)	TP-24			
-03	-P	PT-1-24-14-29	TP-09			
-03	-LC-P, -A-P	PT-1-24-14-29	TP-09			

NOTES:

- 1. LOAD PARTS POSITION 1 FIRST IN SAME DIRECTION AS ARROW.
- 2. NOTE DELETED
- 3. PACKAGE POSITIONS -04 THRU -36.
- 4. POLARIZED 4 POSITION PARTS WITHOUT PADS ARE TO BE LAYER PACKAGED OR PACKAGED IN TAPE AND REEL.








FIG 5 -TR: TAPE & REEL PACKAGNG OPTION



USER DIRECTION OF UN-REELING POCKET NOT DETAILED



F:\DWG\MISC\MKTG\TSM-1XX-XXX-SV-XX-XXX-XXX-MKT.SLDDRW

* PROPRIETARY NOTE *			
THIS DOCUMENT CONTAINS CONFIDENTIAL AND			
PROPRIETARY INFORMATION AND ALL DESIGN,	Comion		
MANUFACTURING, REPRODUCTION, USE, PATENT RIGHTS			
AND SALES RIGHTS ARE EXPRESSLY RESERVED BY SAMTEC,			
INC. THIS DOCUMENT SHALL NOT BE DISCLOSED, IN WHOLE			
OR PART, TO ANY UNAUTHORIZED PERSON OR ENTITY NOR	520 PARK EAST BLVD, NEW ALBANY, IN 47150		
REPRODUCED, TRANSFERRED OR INCORPORATED IN ANY	PHONE: 812-944-6733 FAX: 812-948-5047		
OTHER PROJECT IN ANY MANNER WITHOUT THE EXPRESS	e-Mail info@SAMTEC.com code 55322		
WRITTEN CONSENT OF SAMTEC, INC.	e-Mail IIII0@3AMILC.COIII Code 33322		
DO NOT SCALE DRAWING	DESCRIPTION:		
DO NOT SCALL DIAMING	SINGLE ROW .100 SMT ASSEM		

SINGLE ROW . 100 SMT ASSEMBLY

DWG. NO. TSM-1XX-XX-XXX-SV-XX-XXX-XX

BY: DEAN P 8/21/2002 SHEET 2 OF 2

SHEET SCALE: 2:1