
REVISION BN

DO NOT CALE FROM THIS PRINT

	TABLE 2	
No OF POS	"A"	"B"
-020	.838 [21.27]	.793 [20.13]
-040	1.625 [41.28]	1.580 [40.13]
-060	2.413 [61.28]	2.368 [60.13]
*-080	3.200 [81.28]	3.155 [80.14]
*-100	3.988 [101.28]	3.943 [100.14]

TABLE 1		
No OF POS	COPLANARITY	
NO OF POS	INCLUDING GP	
-020 THRU -040	.004[0.10]	
-060, *-080, *-100	.006[0.15]	

(*= SEE NOTE 17)



QSE-XXX-01-XXX-D-XXX No OF POSITIONS -020, -040, -060 *-080, *-100 (PER ROW) (*= SEE NOTE 17) LEAD STYLE -01: .1280[3.251]

PLATING SPECIFICATION

(SEE NOTES 8, 11 & 13) -F: 3u" SELECTIVE GOLD IN CONTACT AREA, MATTE TIN ON TAIL (USE C-126-21-F, T-1G2-01-F) (SEE NOTE 8)
-L: 10µ" SELECTIVE GOLD IN CONTACT AREA, MATTE TIN ON TAIL (USE C-126-21-L, T-1G2-01-L) -H: 30µ" GOLD IN CONTACT ÁREA 3µ" GOLD ON TAIL

(USE C-126-21-H, T-1G2-01-G)
-C: 50µ" ELECTRO POLISHED SELECTIVE GOLD IN CONTACT AREA, MATTE TIN ON TAIL (USE C-126-21-C, T-1G2-01-L) -STL: 30µ" SELECTIVE GOLD IN CONTACT

AREA, TIN LEAD (90/10 ±5%) ON TAIL (USE C-126-21-STL, T-1G2-01-STL) -FTL: 3u" SELECTIVE GOLD INCONTACT AREA, TIN LEAD (90/10 ±5%) ON TAIL

(USE C-126-21-FTL, T-1G2-01-FTL) 10µ" SELECTIVE GOLD IN CONTACT AREA, TIN LEAD (90/10 ±5%) ON TAIL (USE C-126-21-LTL, T-1G2-01-LTL) -S: 30µ" SELECTIVE GOLD IN CONTACT AREA, MATTE TIN ON TAIL

(USE C-126-21-S, T-1G2-01-L)

OPTION -A: ALIGNMENT PINS (USE QSE-20-XX-D-XX-A) (NOT AVAILABLE WITH -LC OPTION) -LC: LOCKING CLIPS (SEE NOTE 14) (USE LC-08-TM-01, SEE FIG 2, SHT 2) (NOT AVAILABLE WITH -A OPTION) -GP: GUIDE POSTS (SEE FIG 4, SHT 3) (USE QSE-20-01-D-XX-X-GP) T & R PACKAGING: 40 POS MAX) -K: POLYIMIDE FILM (USE K-DOT-.325-.450-.005) (SEE FIG 3, SHT 2) -TR: TAPE & REEL (60 POS MAX)

(SEE FIG 8, SHT 5) (40 POS MAX -GP OPTION) (SEE NOTE 19)
-FL: FRICTION LOCKS
(SEE FIG 5, SHT 3)
(NOT AVAILABLE WITH -GP) -RT1: RETENTION OPTION (MUST USE -A OPTION) USE QSE-20-01-D-XX-A-RT1 & SUB-SC-05-01-FF) (SEE FIG 6, SHT 4) (NOT AVAILABLE WITH -LC, -GP, OR -FL) (NOT AVAILABLE WITH -100 POS) -L: LATCHING OPTION (40 POS MAX) (SEE FIG 7, SHT 4) (MUST USE -A OPTION) (NOT AVAILABLE WITH -LC, -GP, -FL, OR -RT1)

-FR: FULL REEL QTY, TAPE & REEL(60 POS MAX) (40 POS MAX -GP OPTION) (SEE NOTE 20) ROW SPECIFICATION

(USE QSE-20-XX-D-XX) No OF BANKS

.017±.005 0.43±0.13 (SEE NOTE 16) .0030 [0.076] REF $\langle \mathbb{C} \rangle$ $.1280^{+.0030}_{-.0010}$ $3.251^{+0.076}_{-0.025}$ (SEE NOTE 6 & 7) $\langle C \rangle$ SEE TABLE 1 \bigcirc .064 1.62 REF .007 0.18 REF C-126-21-XXX (SEE NOTE 13) SECTION "A"-"A"

FIG 1 -A: ALIGNMENT PIN OPTION (QSE-060-01-XXX-D-A SHOWN)

UNLESS OTHERWISE SPECIFIED.

DIMENSIONS ARE IN INCHES. TOLERANCES ARE: DECIMALS **ANGLES** .XX: ±.01[.3] .XXX: ±.005[.13] 2°

THIS DOCUMENT CONTAINS CONFIDENTIAL AND PROPRIETARY INFORMATION AND ALL DESIGN, MANUFACTURING REPRODUCTION, USE PATENT RIGHTS AND SALES RIGHTS ARE EXPRESSLY RESERVED BY SAMTEC, INC. THIS DOCUMENT SHALL NOT BE DISCLOSED. IN WHOLE OR PART, TO ANY UNAUTHORIZED PERSON OR ENTITY NOR REPRODUCED, TRANSFERRED OR INCORPORATED IN ANY OTHER PROJECT IN ANY MANNER WITHOUT THE EXPRESS

SHEET SCALE: 1.5:1

WRITTEN CONSENT OF SAMTEC INC

PROPRIETARY NOTE

520 PARK EAST BLVD, NEW ALBANY, IN 47150 PHONE: 812-944-6733 FAX: 812-948-5047

e-Mail info@SAMTEC.com code 55322

DESCRIPTION

BY: ERIC M

.8mm DOUBLE ROW HS SOCKET ASSEMBLY

05/20/1999 | SHEET 1 OF 5

DWG. NO QSE-XXX-01-XXX-D-XXX

CONTACT: PHOS BRONZE

.XXXX: ±.0020[.051]

INSULATOR: LCP, UL94V-0; COLOR: BLACK GROUND PLANE: PHOS BRONZE

20. -FR OPTIONS WILL BE SHIPPED AT THE MAX QUANTITY PER REEL, BASED OPTIONS

SELECTED

5. DELETED.

12. NOTE DELETED

15. SIDE WALLS ARE RIBBED AS NECESSARY TO CONTROL BOW. 16. CHECK ONCE PER BANK ALTERNATING SIDES FOR MULTIPLE BANK PARTS. 17. AVAILABLE FOR EXISTING CUSTOMERS ONLY.

14. DUE TO THE HIGH AMOUNT OF INSERTION FORCE NEEDED, THE -LC OPTION

IS NOT COMPATIBLE WITH AUTO PLACEMENT. SAMTEC RECOMMENDS

MANUAL PLACEMENT FOR ALL ASSEMBLIES WITH THE -LC OPTION.

8. -L PLATING CAN BE SUBSTITUTED FOR -F PLATING, -G PLATED GROUND

9. GROUND PLANE PRESS HEIGHT MUST BE .003 [0.08] LESS THAN THE MAX HEIGHT OR .001 [0.03] GREATER THAN THE MINIMUM HEIGHT OF THE SOCKETS.

PLANE CAN BE SUBSTITUTED FOR -F PLATED GROUND PLANE.

13. FOR -080, -100 POSITIONS USE C-269-11-XXX. DO NOT SUB C-126.

18. NOTE DELETED

11. MAY SUB C-126-01-XXX FOR C-126-21-XXX.

© REPRESENTS A CRITICAL DIMENSION.

3. MINIMUM GROUND PLANE RETENTION: 8 OZ 4. PARTS ARE MOLDED TO POSITION.

7. DIMENSION APPLIES TO CONTACTS & GROUND PLANE.

10. MINIMUM SUB-SC-05-01-XX RETENTION: 1 LB IN BODY.

© 2. MINIMUM CONTACT RETENTION: 8 OZ


6. MAXIMUM VARIANCE: .002[0.51].

19. -TR OPTION ORDERS INVOLVING PARTIAL REEL QUANTITIES MAY BE PACKAGED ACCORDING TO THE SAMTEC PACKAGING EFFICIENCY STANDARDS (SPES) FOUND ON WWW.SAMTEC.COM.

F:\DWG\MISC\MKTG\QSE-XXX-01-XXX-D-XXX-MKT.SLDDRW

DO NOT SCALE DRAWING

REVISION BN








FIG 2
-LC: LOCKING CLIP OPTION
(QSE-060-01-XXX-D-LC SHOWN)
(DIFFERENT AS SHOWN, OTHERWISE SAME AS FIG 1)

TABLE 3								
No OF POS	"R"			"S"				
110 01 1 00	-LC, -A, -FL	-GP	-RT1	-L	-LC, -A, -FL	-GP	-RT1	-L
-020	.839 [21.31]	1.216 [30.89]	1.438 [36.51]	1.048 [26.61]	.257 [6.53]	.446 [11.32]	.556 [14.13]	.361 [9.18]
-040	1.627 [41.31]	2.004 [50.89]	2.225 [56.52]	1.835 [46.61]	.651 [16.53]	.839 [21.32]	.950 [24.13]	.755 [19.18]
-060	2.417 [61.38]	2.791 [70.89]	3.013 [76.52]	N/A	1.046 [26.56]	1.233 [31.32]	1.344 [34.13]	N/A
*-080	3.204 [81.38]	3.579 [90.89]	3.800 [96.52]	N/A	1.440 [36.56]	1.627 [41.32]	1.738 [44.13]	N/A
*-100	3.991 [101.37]	4.366 [110.90]	N/A	N/A	1.833 [46.56]	2.021 [51.32]	N/A	N/A

(*= SEE NOTE 17)











TABLE 4			
POS	"C"	"D"	
-020	1.216 [30.89]	1.013 [25.72]	
-040	2.004 [50.89]	1.800 [45.72]	
-060	2.791 [70.89]	2.588 [65.72]	
*-080	3.579 [90.89]	3.375 [85.73]	
*-100	4.366 [110.90]	4.163 [105.73]	

(*= SEE NOTE 17)



FIG 4
-GP: GUIDE POST OPTION
(QSE-060-01-XXX-D-A-GP SHOWN)
(DIFFERENT AS SHOWN, OTHERWISE SAME AS FIG 1) (40 POS MAX WITH T & R PACKAGING)



520 PARK EAST BLVD, NEW ALBANY, IN 47150 PHONE: 812-944-6733 FAX: 812-948-5047 e-Mail info@SAMTEC.com code 55322


DESCRIPTION: DO NOT SCALE DRAWING

SHEET SCALE: 2:1

.8mm DOUBLE ROW HS SOCKET ASSEMBLY DWG. NO.

QSE-XXX-01-XXX-D-XXX 05/20/1999 SHEET 3 OF 5 BY: ERIC M

F:\DWG\MISC\MKTG\QSE-XXX-01-XXX-D-XXX-MKT.SLDDRW







TABLE 6					
POS	"G"	"H"	"J"		
-020	1.048 [26.61]	.897 [22.78]	.959 [24.36]		
-040	1.835 [46.61]	1.684 [42.78]	1.747 [44.36]		
-060	N/A	N/A	N/A		
*-080	N/A	N/A	N/A		
*-100	N/A	N/A	N/A		

(*= SEE NOTE 17)



*	PROPRIETARY NOTE	*	
THIS DOO	UMENT CONTAINS CONFIDENTIAL AND		
PROPRIE	TARY INFORMATION AND ALL DESIGN,		
MANUFA	CTURING, REPRODUCTION, USE, PATENT	RIGHTS	
AND SALI	ES RIGHTS ARE EXPRESSLY RESERVED BY S	SAMTEC,	
INC. THIS	DOCUMENT SHALL NOT BE DISCLOSED, I	N WHOLE	
OR PART,	, TO ANY UNAUTHORIZED PERSON OR EN	TITY NOR	
REPRODU	JCED, TRANSFERRED OR INCORPORATED	IN ANY	
OTHER P	ROJECT IN ANY MANNER WITHOUT THE E	XPRESS	
WRITTEN	CONSENT OF SAMTEC, INC.		
			D

DO NOT SCALE DRAWING

SHEET SCALE: 2:1

samtec

520 PARK EAST BLVD, NEW ALBANY, IN 47150 PHONE: 812-944-6733 FAX: 812-948-5047 e-Mail info@SAMTEC.com code 55322

DESCRIPTION:


.8mm DOUBLE ROW HS SOCKET ASSEMBLY

DWG. NO. QSE-XXX-01-XXX-D-XXX


BY: ERIC M 05/20/1999 SHEET 4 OF 5

F:\DWG\MISC\MKTG\QSE-XXX-01-XXX-D-XXX-MKT.SLDDRW

FIG 8
-TR: PACKAGING OPTION
(QSE-060-01-XXX-D-LC-TR SHOWN)
(DIFFERENT AS SHOWN, OTHERWISE SAME AS FIG 1)
(60 POS MAX)
(40 POS MAX WITH -GP OPTION)



USER DIRECTION OF UNREELING POCKET NOT DETAILED



* PROPRIETARY NOTE THIS DOCUMENT CONTAINS CONFIDENTIAL AND PROPRIETARY INFORMATION AND ALL DESIGN, MANUFACTURING, REPRODUCTION, USE, PATENT RIGI

MANUFACTURING, REPRODUCTION, USE, PATENT RIGHTS AND SALES RIGHTS ARE EXPRESSY RESERVED BY SAMITES. INC. THIS DOCUMENT SHALL NOT BE DISCLOSED, IN WHOLE OR PART, TO ANY UNAUTHORIZED PERSON OR ENTITY NOR DEPRODUCED, TRANSFERRED OR HOORPORATED IN ANY OTHER PROJECT IN ANY MANNER WITHOUT THE EXPRESS WRITTEN CONSENTO FO SAMITES, LOSSION OF SAMITES, LO

520 PARK EAST BLVD, NEW ALBANY, IN 47150

PHONE: 812-944-6733 FAX: 812-948-5047 e-Mail info@SAMTEC.com code 55322

DO NOT SCALE DRAWING

SHEET SCALE: 2:1

DESCRIPTION:

.8mm DOUBLE ROW HS SOCKET ASSEMBLY

DWG. NO.

QSE-XXX-01-XXX-D-XXX

BY: ERIC M 05/20/1999 SHEET 5 OF 5