


REVISION K


DO NOT SCALE FROM THIS PRINT

-D (DOUBLE END)




-S (SINGLE END)

SAME AS -D (DOUBLE)  
UNLESS OTHERWISE NOTED




-T (TRANSFER)

SAME AS -D (DOUBLE)  
UNLESS OTHERWISE NOTED



|                          |                           |                              |                              |                 |  |  |  |  |
|--------------------------|---------------------------|------------------------------|------------------------------|-----------------|--|--|--|--|
| DIMENSIONS ARE IN INCHES |                           | UNLESS OTHERWISE NOTED       |                              | TOLERANCES ARE: |  | TITLE: .050 DOUBLE ROW MALE IDC CABLE ASSEMBLY |  | DWG NO: FFMD-XX-X-XX-01-X-XXX-XXX SHEET 1 OF 1 |
| ONE PLACE DECIMALS: ± .1 | TWO PLACE DECIMALS: ± .01 | THREE PLACE DECIMALS: ± .005 | FOUR PLACE DECIMALS: ± .0020 | ANGLES: ± 1°    |  |  |  |  |




| 1            | 2                    | 3          |
|--------------|----------------------|------------|
| FFSD-XX-01-X | CB-XX-30-7/38-025-GR | FFMD-XX-01 |


SPECIFY NO. OF POS. IN PART CALLOUT -XX

NOTES:  
1. HIDDEN LINES ARE USED TO SHOW POLARIZATION WHEN USING -N OPTION.  
2. Ⓞ REPRESENTS CRITICAL DIMS FOR STATISTICAL PROCESS CONTROL.  
3. TABLE 1: PART #1 TO BE USED FOR TRANSFER END ONLY.  
4. ALL ASSEMBLIES TO BE 100% ELECTRICALLY TESTED FOR SHORTS AND OPENS.  
5. ALL ASSEMBLIES TO BE 100% HI-POT TESTED AT 630V.


-O OUTSIDE REVERSED




-M MIDDLE REVERSED




-R REVERSE CONNECTOR



-D"XX" DAISY CHAIN-DOUBLE




-BXX BREAKOUT OPTION




|                          |
|--------------------------|
| -T: TIN (STANDARD)       |
| -L: SELECTIVE LIGHT GOLD |
| -F: FLASH SELECTIVE GOLD |
| -S: SELECTIVE GOLD       |


-O OUTSIDE REVERSED (TRANSFER)




-M MIDDLE REVERSED (TRANSFER)




-R REVERSE CONNECTOR (TRANSFER)




-D"XX" DAISY CHAIN-DOUBLE (TRANSFER)



-N NOTCH POLARIZATION (FOR -T ONLY)



-RW REVERSE WIRING



PROPRIETARY NOTE  
THIS DOCUMENT CONTAINS INFORMATION OF A PROPRIETARY AND CONFIDENTIAL NATURE. IT IS THE PROPERTY OF SAMTEC INC. AND SHALL NOT BE REPRODUCED OR TRANSMITTED IN ANY FORM OR BY ANY MEANS, ELECTRONIC OR MECHANICAL, INCLUDING PHOTOCOPYING, RECORDING, OR BY ANY INFORMATION STORAGE AND RETRIEVAL SYSTEM. WITHOUT THE WRITTEN PERMISSION OF SAMTEC INC.

EQUIPMENT CABLE  
FFMD-ASM

**samtec**

520 PARK EAST BLVD., NEW ALBANY, INDIANA 47150  
PHONE (812) 944-8733 P.O. BOX 1147  
CODE 55322

MADE BY: CHAD F 3/19/2002

FFMD-XX-X-XX-01-X-XXX-XXX SHEET 1 OF 1