



1. MATERIAL:

BODY, OUTER CONTACT, CLAMP NUT: STAINLESS STEEL.
O-RING: SILICONE RUBBER.
SOLDER FERRULE: BRASS.

BEAD: ULTEM.

CONTACT: BERYLLIUM COPPER.

2. FINISH:

BODY, OUTER CONTACT, CLAMP NUT: PASSIVATED. SOLDER FERRULE, PIN: GOLD OVER NICKEL PLATE, 50 µIN MIN GOLD OVER 50 µIN MIN NICKEL.


3.PERFORMANCE:

IMPEDANCE: 50Ω

FREQUENCY: DC TO 50 GHz VSWR: 1.18: 1 MAXIMUM INSERTION LOSS: 0.03 x √f(GHz)

DWV: 1150 Vrms

4. PCI PART NUMBER: 3864.



EXPLODED VIEW
NOT TO SCALE
(FOR CLARITY ONLY)

UNLESS OTHERWISE SPECIFIED, DIMENSIONS ARE IN INCHES. TOLERANCES ARE:

ANGLES

DECIMALS
.XX: ±.01

.XX: ±.01 .XXX: ±.002 .XXXX: ±.0005 * PROPRIETARY NOTE

THIS DOCUMENT CONTAINS CONFIDENTIAL AND
PROPRIETARY INFORMATION AND ALL DESIGN,
MANUFACTURING, REPRODUCTION, USE, PATENT RIGHTS
AND SALES RIGHTS ARE EXPRESSLY RESERVED BY SAMTEC,
INC. THIS DOCUMENT SHALL NOT BE DISCLOSED, IN WHOLE

OR PART, TO ANY UNAUTHORIZED PERSON OR ENTITY NOR

REPRODUCED, TRANSFERRED OR INCORPORATED IN ANY

OTHER PROJECT IN ANY MANNER WITHOUT THE EXPRESS WRITTEN CONSENT OF SAMTEC, INC.

DO NOT SCALE DRAWING

SHEET SCALE: 3:1



520 PARK EAST BLVD, NEW ALBANY, IN 47150 PHONE: 812-944-6733 FAX: 812-948-5047 e-Mail info@SAMTEC.com code 55322

DESCRIPTION:

2.4MM JACK. SOLDER CLAMP FOR HARBOUR SS405

DWG. NO.

PRF24-J-C-EP-085-SS

BY: EVE L

04/29/2019 SHEET 1 OF 2


F:\DWG\MISC\MKTG\PRF24-J-C-EP-085-SS-MKT.SLDDRW

REVISION B

1A. TRIM CABLE JACKET TO EXPOSE DIELECTRIC & CENTER CONDUCTOR AS SHOWN.


1B. POINT CENTER CONDUCTOR AS SHOWN.

IN-PROCESS 1



2A. SLIDE CLAMP NUT OVER CABLE AS SHOWN.

- 2B. INSTALL CABLE INTO SOLDER FERRULE UNTIL SEATED AND SOLDER WHERE SHOWN.
- 2C. TRIM CABLE DIELECTRIC FLUSH TO FACE OF SOLDER FERRULE (DO NOT NICK CENTER CONDUCTOR)
- 2D. INSTALL O-RING INTO GROOVE IN SOLDER FERRULE FLANGE AS SHOWN.



IN-PROCESS 2

