


TABLE 3			
STYLE	No. OF POS	"F"	"G"
Standard With -GP Option	-20	1.770 [44.96]	1.533 [38.94]
	-30	2.270 [57.66]	2.033 [51.64]
	-40	2.770 [70.36]	2.533 [64.34]
	-50	3.270 [83.06]	3.033 [77.04]
Without -gp option	-20	1.435 [36.45]	N/A
	-30	1.935 [49.15]	
	-40	2.435 [61.85]	
	-50	2.935 [74.55]	








FIG 2 WITHOUT -GP OPTION SEAFP-20-01-X-08-RA-WT SHOWN (SAME AS FIG 1, EXCEPT AS SHOWN) (SOME CENTER FEATURES REMOVED FOR CLARITY)





F:\DWG\MISC\MKTG\SEAFP-XX-XX-XX-RA-XX-XX-MKT.SLDDRW



**REVISION G** 

