REVISION C

5/22/2017 ECN-301423

DO NOT SCALE FROM THIS PRINT

QXH MATED VIEWS

DESIGNED & DIMENSIONED IN INCHES[MILLIMETERS]

FIGURE 1 FIGURE 2


QSH-D-XX MATED WITH QTH-D-XX QTH-D-XX MATED WITH QSH-D-XX-EMX


FIGURE 3


QSH-D-XX MATED WITH QTH-D-XX-EMX

FIGURE 4

QSH-D-XX-EMX MATED WITH QTH-D-XX-EMX











FIGURE 5 QSH-D-XX-RA MATED WITH QTH-D-XX-RA

| TABLE 2 | | | TABLE 3 | | |
|-------------------|-----|-----------------|----------|-----|-------------------|
| | | QSH- LEAD STYLE | | | QSH-EM LEAD STYLE |
| | | -01 | | | -01 |
| QTH LEAD STYLE | -01 | .198 [5.03] | | -01 | .365 [9.27] |
| | -02 | .316 [8.03] | | -02 | .483 [12.27] |
| | -03 | .434 [11.03] | | -03 | .601 [15.27] |
| | -04 | .630 [16.00] | QTH LEAD | -04 | .797 [20.25] |
| | -05 | .748 [19.00] | | -05 | .915 [23.24] |
| | -06 | .866 [22.00] | STYLE | -06 | 1.033 [26.24] |
| | -07 | .984 [25.00] | | -07 | 1.151 [29.24] |
| | -08 | 1.181 [30.00] | | -08 | 1.348 [34.24] |
| | -09 | .552 [14.03] | | -09 | .719 [18.27] |
| | -10 | .592 [15.03] | | -10 | .759 [19.27] |



| TABLE 1 | | | | | | | |
|------------------------|---|---------------------------------------|--|---|------------------|------------------|--|
| | Fully Mated Board to Board Dimension ("A") | Max Board to Board Dimension ("A") | Fully Mated Connector to Connector Dimension ("B") | Max Connector to Connector Dimension ("B") | Min Contact Wipe | Max Contact Wipe | |
| FIG 1) QSH / QTH | See Table 2 | = Stack Height + .007 [.178] | N/A | N/A | .015 [0.381] | .022 [0.56] | |
| FIG 2) QTH / QTH-EM | N/A | N/A | See Table 3 | = Stack Height + .007 [.178] | .015 [0.381] | .022 [0.56] | |
| FIG 3) QSH / QTH-EM | N/A | N/A | 0.366 [9.30] | 0.373 [9.47] | .015 [0.381] | .022 [0.56] | |
| FIG 4) QSH-EM / QTH-EM | N/A | N/A | 0.532 [13.51] | 0.539 [13.69] | .015 [0.381] | .022 [0.56] | |
| FIG 5) QSH-RA/QTH-RA | 0.007 [0.18] | 0.028 [0.71] | 0.927 [23.55] | 0.948 [24.08] | .015 [0.381] | .036 [0.91] | |

NOTES:

- 1. ALL DIMENSIONS BASED ON NOMINAL VALUES FOR SAMTEC RECOMMENDED PCB LAYOUTS.
- 2. ALTHOUGH MAX DIMENSIONS ARE LISTED SAMTEC RECOMMENDS FULLY MATING COMPONENTS.

THIS DOCUMENT CONTAINS CONDIDENTIAL AND PROPRIETARY NOTE

THIS DOCUMENT CONTAINS CONDIDENTIAL AND PROPRIETARY INFORMATION AND ALL DESIGN, MANUFACTURING, REPRODUCTION, USE, PATENT RIGHTS AND SALES RIGHTS ARE EXPRESSLY RESERVED BY SANTEC, INC. THIS DOCUMENT SHALL NOT BE DISCLOSED, IN WHOLE OR PART, TO ANY UNAUTHORIZED PERSON OR ENTITY NOR REPRODUCED, TRANSFERRED OR INCORPORATED IN ANY OTHER PROJECT IN ANY MANNER WITHOUT THE EXPRESS WRITTEN CORSENT OF SANTEC.



QXH MATED VIEWS




FIGURE 6
QSH-D-XX MATED WITH QTH-D-XX-RA

| TABLE 4: STACK HEIGHTS - FULLY MATED | | | | | | |
|--------------------------------------|-----|--------------------|--------|------|---------|--|
| | | QTH- RA LEAD STYLE | | | | |
| | | -01 | | | | |
| | | "A" "C" | | | D" | |
| QSH LEAD STYLE | -01 | .135 | [3.43] | .535 | [13.59] | |
| | -11 | .136 | [3.45] | .536 | [13.61] | |




FIGURE 7 QTH-D-XX MATED WITH QSH-D-XX-RA

| TABLE 5: STACK HEIGHTS - FULLY MATED | | | | | | | |
|--------------------------------------|-----|--------------------|---------|-------|---------|--|--|
| | | QSH- RA LEAD STYLE | | | | | |
| | | -01 | | | | | |
| | | "A" | | "C" | | | |
| | -01 | .070 | [1.78] | .590 | [14.99] | | |
| | -02 | .188 | [4.78] | .708 | [17.99] | | |
| | -03 | .306 | [7.78] | .826 | [20.99] | | |
| | -04 | .502 | [12.75] | 1.022 | [25.96] | | |
| QTH LEAD | -05 | .620 | [15.75] | 1.140 | [28.96] | | |
| STYLE | -06 | .738 | [18.75] | 1.258 | [31.96] | | |
| | -07 | .856 | [21.75] | 1.376 | [34.96] | | |
| | -08 | 1.053 | [26.75] | 1.573 | [39.96] | | |
| | -09 | .126 | [3.20] | .646 | [16.41] | | |
| | -10 | .464 | [11.78] | .984 | [24.99] | | |

| TABLE 6 | | | | | | |
|---------------------|--|---|--|---|--|--|
| Mated Pair | Fully Mated Board to Board Dimension "A" with Contact Wipe of .018" [0.46mm] | Maximum Allowable Board to Board Dimension "A" to Maintain Minimum Contact Wipe of .015" [0.38mm] | Fully Mated Connector to Board Dimension "C" with Contact Wipe of .018" [0.46mm] | Maximum Allowable Connector to Board Dimension "C" to Maintain Minimum Contact Wipe of .015" [0.38mm] | | |
| FIG 6) QSH / QTH-RA | SEE TABLE 4 | TABLE 4 "A" DIM + .003" [0.08mm] | SEE TABLE 4 | TABLE 4 "C" DIM+ .003" [0.08mm] | | |

| TABLE 7 | | | | | | |
|---------------------|--|---|--|---|--|--|
| Mated Pair | Fully Mated Board to Board Dimension "A" with Contact Wipe of .040" [1.02mm] | Maximum Allowable Board to Board Dimension "A" to Maintain Minimum Contact Wipe of .015" [0.38mm] | Fully Mated Connector to Board Dimension "C" with Contact Wipe of .040" [1.02mm] | Maximum Allowable Connector to Board Dimension "C" to Maintain Minimum Contact Wipe of .015" [0.38mm] | | |
| FIG 7) QTH / QSH-RA | SEE TABLE 5 | TABLE 5 "A" DIM + .025" [0.64mm] | SEE TABLE 5 | TABLE 5 "C" DIM+ .025" [0.64mm] | | |

THIS DOCUMENT CONTAINS CONFIDENTIAL AND
PROPRIETARY INFORMATION AND ALL DESIGN,
MANUFACTURING, REPRODUCTION, USE, PATENT RIGHTS
AND SALES REGITS ARE EXPRESSLY SERSEWED BY SAMPLE,
INC. THIS DOCUMENT SHALL NOT BE DISCLOSED, IN WHOLE
OR PART, TO ANY UNALITHORIZED PERSON OR ENTITY NOR
REPRODUCED, TRANSFERRED ON MOORPORATE IN ANY
OTHER PROJECT IN ANY MANNER WITHOUT THE EXPRESS
WRITTEN CONSENT OF SAMPLE, IN

