DESIGNED AND DIMENSIONED IN MILLIMETERS[INCHES] REVISION F UMPT-XX-XX-XX-RA-WX-X-XR **ALL DIMENSIONS REFERENCE EXCEPT AS SHOWN** No OF POSITIONS TAPE & REEL (SEE NOTE 3 & 4) DO NOT -02, -03, -04, -05, -TR: TAPE & REEL "A"±0.08["A"±.003] SCALE FROM -06, -07, -08, -09, -FR: FULL REEL QTY TAPE & REEL THIS PRINT **LATCH OPTIONS LEAD STYLE** (LEAVE BLANK FOR NO LATCH) -01: SURFACE MOUNT -P: PLASTIC TOP LATCH -M: METAL SIDE LATCHES WELD TAB OPTIONS **PLATING** -WT: WELD TAB THROUGH HOLE -T: MATTE TIN *-WS: WELD TAB SURFACE MOUNT -L: 10µ" SELECTIVE GOLD IN CONTACT AREA, MATTE TIN ON TAIL, 9.75±0.05 [.384±.002] **ORIENTATION** MATTE TIN ON THE WELD TAB. -RA: RIGHT ANGLE -S: 30µ" SELECTIVE GOLD IN CONTACT AREA, MATTE TIN ON TAIL. MATTE TIN ON THE WELD TAB -SL: 30µ" SELECTIVE GOLD IN CONTACT (* = NOT TOOLED) AREA, TIN-LEAD ON TAIL, TIN-LEAD ON THE WELD TAB. 01 04 9.65±0.05 380±.002 -0.05±0.10[.002±.004] 1.40[.055] (TYP)- \mathbf{u} 2.00 .079 2.00 .079 0.25[.010] (TYP) (TYP) 5.75 .226 0.64 .025 TABLE 1

		No. OF POS	"A"	"B"	"C"	"D"
4		-02	13.60 [.535]	4.20 [.165]	2.00 [.079]	11.10 [.437]
<u> </u>		-03	15.60 [.614]	6.20 [.244]	4.00 [.157]	13.10 [.516]
· I		-04	17.60 [.693]	8.20 [.323]	6.00 [.236]	15.10 [.594]
		-05	19.60 [.772]	10.20 [.402]	8.00 [.315]	17.10 [.673]
₩		-06	21.60 [.850]	12.20 [.480]	10.00 [.394]	19.10 [.752]
1	<u>FIG 1</u>	-07	23.60 [.929]	14.20 [.559]	12.00 [.472]	21.10 [.831]
	/ UMPT-04-01-XX-RA-WT SHOWN	-08	25.60 [1.008]	16.20 [.638]	14.00 [.551]	23.10 [.909]
		-09	27.60 [1.087]	18.20 [.717]	16.00 [.630]	25.10 [.988]
		-10	29.60 [1.165]	20.20 [.795]	18.00 [.709]	27.10 [1.067]

NOTES:

- 1. NOTE DELETED.
- 2. NOTE DELETED.
- 3. ATTACH LABEL -4x2 TO EACH REEL.
 4. ORDERS WILL BE PACKAGED ACCORDING TO THE SAMTEC PACKAGING EFFICIENCY STANDARDS (SPES) FOUND ON WWW.SAMTEC.COM.

PROPRIETARY NOTE

THIS DOCUMENT CONTAINS CONFIDENTIAL AND PROPRIETARY INFORMATION AND ALL DESIGN, MANUFACTURING, REPRODUCTION, USE, PATENT RIGHTS AND SALES RIGHTS ARE EXPRESSLY RESERVED BY SAMTEC, INC. THIS DOCUMENT SHALL NOT BE DISCLOSED, IN WHOLE OR PART, TO ANY UNAUTHORIZED PERSON OR ENTITY NOR REPRODUCED, TRANSFERRED OR INCORPORATED IN ANY OTHER PROJECT IN ANY MANNER WITHOUT THE EXPRESS WRITTEN CONSENT OF SAMTEC INC

DO NOT SCALE DRAWING

INSULATOR: LCP TERMINAL: COPPER ALLOY WELD TAB: COPPER ALLOY



520 PARK EAST BLVD, NEW ALBANY, IN 47150 PHONE: 812-944-6733 FAX: 812-948-5047 e-Mail info@SAMTEC.com

DESCRIPTION

ULTRA MICRO POWER RA TERMINAL


BY: ETHAN C

UMPT-XX-XX-XX-RA-WX-X-XR

F:\DWG\MISC\MKTG\UMPT-XX-XX-XX-RA-WX-X-XR-MKT.SLDDRW

06/12/2019 | SHEET 1 OF 2

REVISION F






FIG 2 UMPT-04-01-XX-RA-WT-P SHOWN (DIFFERENT AS SHOWN, OTHERWISE SAME AS FIG 1)






FIG 3 UMPT-04-01-XX-RA-WT-M SHOWN (DIFFERENT AS SHOWN, OTHERWISE SAME AS FIG 1)

TABLE 2				
No. OF POS	"E"			
-02	11.55 [.455]			
-03	13.55 [.533]			
-04	15.55 [.612]			
-05	17.55 [.691]			
-06	19.55 [.770]			
-07	21.55 [.848]			
-08	23.55 [.927]			
-09	25.55 [1.006]			
-10	27.55 [1.085]			





PROPRIETARY NOTE

THIS DOCUMENT CONTAINS CONFIDENTIAL AND PROPRIETARY INFORMATION AND ALL DESIGN, MANUFACTURING, REPRODUCTION, USE, PATENT RIGHTS AND SALES RIGHTS ARE EXPRESSLY RESERVED BY SAMTEC, INC. THIS DOCUMENT SHALL NOT BE DISCLOSED, IN WHOLE OR PART, TO ANY UNAUTHORIZED PERSON OR ENTITY NOR REPRODUCED, TRANSFERRED OR INCORPORATED IN ANY OTHER PROJECT IN ANY MANNER WITHOUT THE EXPRESS WRITTEN CONSENT OF SAMTEC, INC.

SHEET SCALE: 2:1

INSULATOR: LCP
TERMINAL: COPPER ALLOY
WELD TAB: COPPER ALLOY

DO NOT SCALE DRAWING DESCRIPTION

BY: ETHAN C

e-Mail info@SAMTEC.com code 55322 ULTRA MICRO POWER RA TERMINAL

PHONE: 812-944-6733

UMPT-XX-XX-XX-RA-WX-X-XR

F:\DWG\MISC\MKTG\UMPT-XX-XX-XX-RA-WX-X-XR-MKT.SLDDRW

06/12/2019 SHEET 2 OF 2

FAX: 812-948-5047